

SFP-25G-LR-S-I-300M-C

Cisco® SFP-25G-LR-S-I Compatible TAA 25GBase-LRL SFP28 Transceiver Capable (SMF, 1310nm, 300m, LC, DOM, -40 to 85C)

Features:

- SFF-8402 and SFF-8472 Compliance
- Duplex LC Connector
- Single-mode Fiber
- Industrial Temperature -40 to 85 Celsius
- Hot Pluggable
- Metal with Lower EMI
- Excellent ESD Protection
- RoHS Compliant and Lead Free



Applications:

- 25GBase Ethernet
- Access and Enterprise

Product Description

This Cisco® SFP-25G-LR-S-I-300M compatible SFP28 transceiver provides 25GBase-LRL throughput up to 300m over single-mode fiber (SMF) using a wavelength of 1310nm via an LC connector. It is guaranteed to be 100% compatible with the equivalent Cisco® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. Digital optical monitoring (DOM) support is also present to allow access to real-time operating parameters. This transceiver is Trade Agreements Act (TAA) compliant. We stand behind the quality of our products and proudly offer a limited lifetime warranty.

ProLabs' transceivers are RoHS compliant and lead-free.

TAA refers to the Trade Agreements Act (19 U.S.C. & 2501-2581), which is intended to foster fair and open international trade. TAA requires that the U.S. Government may acquire only "U.S. – made or designated country end products."



Absolute Maximum Ratings

| Parameter | Symbol | Min. | Тур. | Max. | Unit | Notes |
|---|--------|------|-------|--------------------|------|-------|
| Supply Voltage | Vcc | -0.5 | | 4.0 | V | |
| Storage Temperature | TS | -40 | | 85 | °C | |
| Operating Case Temperature | Тс | -40 | 25 | 85 | °C | |
| Relative Humidity | RH | 5 | | 95 | % | |
| Data Rate | BR | | 25.78 | | Gb/s | |
| Bit Error Rate | BER | | | 5x10 ⁻⁵ | | 1 |
| Supported Link Length on 9/125um SMF, 25.78GB/s | L | | 10 | | km | 2 |

Notes:

- 1. Tested with a PRBS 231-1 test pattern for 25.78Gb/s operation.
- 2. Distances are based on FC-PI-6 Rev 3.1 and IEEE 802.3 standards.

Electrical Characteristics

| Parameter | | Symbol | Min | Тур | Max | Unit | Notes |
|-----------------------------------|----------------------|-----------|-------|-------|---------|-------|-------|
| Supply Voltage | | Vcc | 3.135 | 3.3 | 3.465 | V | |
| Data Rate | | | | 25.78 | | GB/s | |
| Module Supply Current | | Icc | | | 450 | mA | |
| Power Dissipation | | PD | | | 1500 | mW | |
| Transmitter | | | | | | | |
| Input Differential Impedance | | ZIN | | 100 | | Ω | |
| Differential Data Input Swing | | VIN, P-P | 180 | | 700 | mVP-P | |
| TX_FAULT | Transmitter Fault | VOH | 2.0 | | VCCHOST | V | |
| | Normal Operation | VOL | 0 | | 0.8 | V | |
| TX_DISABLE | Transmitter Disable | VIH | 2.0 | | VCCHOST | V | |
| | Transmitter Enable | VIL | 0 | | 0.8 | V | |
| Receiver | | | | | | | |
| Output Differential Impedance | | ZO | | 100 | | Ω | |
| Differential Data Output Swing | | VOUT, P-P | 300 | | 850 | mVp-p | 1 |
| Data Output Rinse Time, Fall Time | | tr, tf | 15 | | | Ps | 2 |
| Rx_LOS | Loss of Signal (LOS) | VOH | 2.0 | | VCCHOST | V | 3 |
| | Normal Operation | VOL | 0 | | 0.8 | V | 3 |

Notes:

- 1. Internally AC coupled, but requires an external 100Ω differential load termination.
- 2. 20-80%
- 3. LOS is an open collector output. Should be pulled up with 4.7Ω on the host board.

Optical Characteristics

| Parameter Parameter | Symbol | Min | Тур | Max | Unit | Notes |
|------------------------------------|--------|------|------|-------|------|-------|
| Transmitter | | | | | | |
| Launch Optical Power | Ро | -5 | | 2 | dBm | 1 |
| Extinction Ratio | ER | 4 | | | dB | |
| Center Wavelength Range | λς | 1295 | 1310 | 1325 | nm | |
| Optical Modulation Amplitude | OMA | 631 | | | uW | |
| Transmitter Dispersion Penalty | TDP | | | 2.7 | dB | |
| Spectral Width | Δλ | | | 1 | nm | 2 |
| Optical Rise/Fall Time @25.78 Gb/s | tr/tf | | | 15 | ps | 3 |
| Optical Return Loss Tolerance | ORLT | | | 12 | dB | |
| Pout @TX-Disable Asserted | POFF | | | -30 | dBm | 1 |
| Receiver | | | | | | |
| Center Wavelength | λc | 1260 | 1310 | 1370 | nm | |
| Receiver OMA Sensitivity | RxSENS | | | -11.4 | dBm | 4 |
| Receiver Overload (P avg) | POL | 2 | | | dBm | |
| Optical Return Loss | ORL | 26 | | | dB | |
| LOS De-Assert | LOSD | | | -13 | dBm | |
| LOS Assert | LOSA | -30 | | | dBm | |
| LOS Hysteresis | | 0.5 | | | dB | |

Notes:

- 1. Class 1 Laser Safety per FDA/CDRH and EN (IEC) 60825 regulations.
- 2. 20dB spectral width.
- 3. Unfiltered, 20-80%.
- 4. Measured with PRBS 2³¹-1 at 5×10⁻⁵ BER


Pin Descriptions

| Pin | Symbol | Name/Descriptions | Notes |
|-----|------------|---|-------|
| 1 | VeeT | Transmitter Ground | 1 |
| 2 | TX_Fault | Transmitter Fault (LVTTL-O) - High indicates a fault condition | 2 |
| 3 | TX_Disable | Transmitter Disable (LVTTL-I) – High or open disables the transmitter | 3 |
| 4 | SDA | Two wire serial interface Data Line (LVCMOS-I/O) (MOD-DEF2) | 4 |
| 5 | SCL | Two wire serial interface Clock Line (LVCMOS-I/O) (MOD-DEF1) | 4 |
| 6 | MOD_ABS | Module Absent (Output), connected to VeeT or VeeR in the module | 5 |
| 7 | RSO | | 6 |
| 8 | RX_LOS | Receiver Loss of Signal (LVTTL-O) | 2 |
| 9 | RS1 | | 6 |
| 10 | VeeR | Receiver Ground | 1 |
| 11 | VeeR | Receiver Ground | 1 |
| 12 | RD- | Inverse Received Data out (CML-O) | |
| 13 | RD+ | Received Data out (CML-O) | |
| 14 | VeeR | Receiver Ground | |
| 15 | VccR | Receiver Power - +3.3V | |
| 16 | VccT | Transmitter Power - +3.3 V | |
| 17 | VeeT | Transmitter Ground | 1 |
| 18 | TD+ | Transmitter Data In (CML-I) | |
| 19 | TD- | Inverse Transmitter Data In (CML-I) | |
| 20 | VeeT | Transmitter Ground | 1 |


Notes:

- 1. The module signal grounds are isolated from the module case.
- 2. This is an open collector/drain output that on the host board requires a $4.7K\Omega$ to $10K\Omega$ pull-up resistor to VccHost.
- 3. This input is internally biased high with a $4.7K\Omega$ to $10K\Omega$ pull-up resistor to VccT.
- 4. Two-Wire Serial interface clock and data lines require an external pull-up resistor dependent on the capacitance load.
- 5. This is a ground return that on the host board requires a $4.7K\Omega$ to $10K\Omega$ pull-up resistor to VccHost.
- 6. Rate select can also be set through the 2-wire bus in accordance with SFF-8472 v. 12.1, Rx Rate Select is set at Bit 3, Byte 110, Address A2h. Tx Rate Select is set at Bit 3, Byte 118, Address A2h. Note: writing a "1" selects maximum bandwidth operation. Rate select is the logic OR of the input state of Rate Select Pin and 2-wire bus.


Electrical Pin-Out Details




Recommended Host Board Power Supply Filter Network




Recommended Application Interface Block Diagram



Mechanical Specifications





About ProLabs

Our experience comes as standard; for over 15 years ProLabs has delivered optical connectivity solutions that give our customers freedom and choice through our ability to provide seamless interoperability. At the heart of our company is the ability to provide state-of-the-art optical transport and connectivity solutions that are compatible with over 90 optical switching and transport platforms.

Complete Portfolio of Network Solutions

ProLabs is focused on innovations in optical transport and connectivity. The combination of our knowledge of optics and networking equipment enables ProLabs to be your single source for optical transport and connectivity solutions from 100Mb to 400G while providing innovative solutions that increase network efficiency. We provide the optical connectivity expertise that is compatible with and enhances your switching and transport equipment.

Trusted Partner

Customer service is our number one value. ProLabs has invested in people, labs and manufacturing capacity to ensure that you get immediate answers to your questions and compatible product when needed. With Engineering and Manufacturing offices in the U.K. and U.S. augmented by field offices throughout the U.S., U.K. and Asia, ProLabs is able to be our customers best advocate 24 hours a day.















Contact Information

ProLabs US

Email: sales@prolabs.com Telephone: 952-852-0252

ProLabs UK

Email: salessupport@prolabs.com Telephone: +44 1285 719 600